

## Entris® II Laboratory Balances



turning science **into solutions**

## Entris® II – Best Value in its Class for Basic Weighing Tasks

Every Sartorius balance offers quality, value and consistency

No matter what you're weighing, the new Entris® II is always the right choice. Offering unrivalled value at a budget price, this is the only balance in its class featuring isoCAL, LED touch technology and 12 built-in applications. Backed by almost 150 years of German engineering expertise, and available in 40 different models, you'll easily find an Entris® II balance that exactly meets your specific weighing needs.



# Quality, Value and Consistency

For accurate weighing results you can trust time after time

### Highest quality standards engineered in Germany


- Highly accurate results year in and year out
  - guaranteed via monolithic weigh cell technology invented by Sartorius\*
- Fastest stabilization time in its class
  - using state-of-the-art weighing sensors
- Best repeatability
  - with rectangular weighing pan
- Overload protection
  - rugged design weighs up to a pre-set amount
- Guaranteed reliability
  - with the self-test "@start"
- Made in Germany

### Easy clean for operational efficiency and durability

- High chemical resistance
  - ensured using parts made from hard-wearing polybutylene terephthalate (PBT), stainless steel and glass
- Prevents cross contamination
  - with wipe clean design and easy-to-remove parts

### Effective draft shield

- Minimizes weighing errors caused by electrostatically charged samples
  - using specially coated glass parts



# Innovations in this Weighing Class

For efficient, user-friendly operation

### isoCAL (internal calibration and adjustment) for total assurance of accurate weighing results

- Optimal accuracy and operating convenience
  - using fully automated internal temperature and time-controlled calibration and adjustment feature, unique in this weighing class
- Assures (SOP) compliant operation
  - with self-notification if calibration is outside the normal range

### Hybrid screen for excellent readability and use

- Combines intuitive, wear resistant LED and touch technology
  - provides an easy and clear structured user interface

### Plug-and-play convenience


- Automatically detects Sartorius accessories (e.g. printer, second display)
- Real "PC-direct feature" for easy connection to a PC to transfer weighing data directly into spreadsheets or documents such as Microsoft® Excel or Word

### Data output for dynamic weighing applications

- Configurable time interval for data output

### Easily adapts to your ambient conditions

- With just one click on the home screen



\* may differ for a few models

# Universal Application

## For future-proof assurance

### The right model for each and every task

- Offering a range of 40 models (the largest portfolio in its class), starting from 60 g up to 8,200 g and a readability from 0.1 mg to 1 g—finding the right model to suit any weighing application is simple

### 12 built-in applications with GLP | GMP compliant printout | data output

- Weighing | Dosing
- Counting
- Percentage weighing
- Mixing | Net Total
- Components | Totalizing
- Animal weighing
- Calculation | Free Factor
- Density determination
- Statistics
- Peakhold
- Checkweighing
- Mass unit conversion
- and underfloor weighing feature for bigger samples

### Weighing chamber (where applicable)

- Highest usable weighing chamber height for easy handling of even large containers
- Convenient access to weighing pan
- Easy-to-(re)move top and side sliding doors
- Draft shield can be removed completely

### 8 built-in languages for international operation

- English, German, French, Italian, Spanish, Portuguese, Russian, Polish

### Modern, up-to-date connectivity methods

- Future-proof USB Type C interface
- Industry-proof RS232 9-pin interface
- Backwards compatibility (by using RS232 port)

### Password protection for secure operation

- Protects the balance against unintentional changes



## Entris® II Technical Specifications

Model	Weighing capacity	Readability	Repeatability, typical	Stabilization time, typical	Weighing pan size	Weighing chamber height*	Dimensions (W x D x H)	Calibration and adjustment	
	[g]	[mg]	[mg]	[s]	[mm]	[mm]	[mm]	Internal	External
<b>Analytical balances</b>									
BCE64i-1x	60	0.1	0.1	≤1,5	Ø 90	240	219x317x345	•	•
BCE64-1x	60	0.1	0.1	≤1,5	Ø 90	240	219x317x345	-	•
BCE124i-1x	120	0.1	0.1	≤1,5	Ø 90	240	219x317x345	•	•
BCE124-1x	120	0.1	0.1	≤1,5	Ø 90	240	219x317x345	-	•
BCE224i-1x	220	0.1	0.1	≤1,5	Ø 90	240	219x317x345	•	•
BCE224-1x	220	0.1	0.1	≤1,5	Ø 90	240	219x317x345	-	•
<b>Precision balances</b>									
BCE223i-1x	220	1	1	≤1,0	Ø 120	240	219x317x345	•	•
BCE223-1x	220	1	1	≤1,0	Ø 120	240	219x317x345	-	•
BCE323i-1x	320	1	1	≤1,0	Ø 120	240	219x317x345	•	•
BCE323-1x	320	1	1	≤1,0	Ø 120	240	219x317x345	-	•
BCE423i-1x	420	1	1	≤1,0	Ø 120	240	219x317x345	•	•
BCE423-1x	420	1	1	≤1,0	Ø 120	240	219x317x345	-	•
BCE623i-1x	620	1	1	≤1,0	Ø 120	240	219x317x345	•	•
BCE623-1x	620	1	1	≤1,0	Ø 120	240	219x317x345	-	•
BCE653i-1x	650	1	1	≤1,0	Ø 120	50	219x317x145	•	•
BCE653-1x	650	1	1	≤1,0	Ø 120	50	219x317x145	-	•
BCE622i-1x	620	10	10	≤0,9	182x182	-	219x317x94	•	•
BCE622-1x	620	10	10	≤0,9	182x182	-	219x317x94	-	•
BCE822i-1x	820	10	10	≤0,9	182x182	-	219x317x94	•	•
BCE822-1x	820	10	10	≤0,9	182x182	-	219x317x94	-	•
BCE1202i-1x	1,200	10	10	≤0,9	182x182	-	219x317x94	•	•
BCE1202-1x	1,200	10	10	≤0,9	182x182	-	219x317x94	-	•
BCE2202i-1x	2,200	10	10	≤0,9	182x182	-	219x317x94	•	•
BCE2202-1x	2,200	10	10	≤0,9	182x182	-	219x317x94	-	•
BCE3202i-1x	3,200	10	10	≤0,9	182x182	-	219x317x94	•	•
BCE3202-1x	3,200	10	10	≤0,9	182x182	-	219x317x94	-	•
BCE4202i-1x	4,200	10	10	≤0,9	182x182	-	219x317x94	•	•
BCE4202-1x	4,200	10	10	≤0,9	182x182	-	219x317x94	-	•
BCE6202i-1x	6,200	10	10	≤0,9	182x182	-	219x317x94	•	•
BCE6202-1x	6,200	10	10	≤0,9	182x182	-	219x317x94	-	•
BCE2201i-1x	2,200	100	100	≤0,9	182x182	-	219x317x94	•	•
BCE2201-1x	2,200	100	100	≤0,9	182x182	-	219x317x94	-	•
BCE5201i-1x	5,200	100	100	≤0,9	182x182	-	219x317x94	•	•
BCE5201-1x	5,200	100	100	≤0,9	182x182	-	219x317x94	-	•
BCE8201i-1x	8,200	100	100	≤0,9	182x182	-	219x317x94	•	•
BCE8201-1x	8,200	100	100	≤0,9	182x182	-	219x317x94	-	•
BCE6200i-1x	6,200	1,000	1,000	≤0,9	182x182	-	219x317x94	•	•
BCE6200-1x	6,200	1,000	1,000	≤0,9	182x182	-	219x317x94	-	•
BCE8200i-1x	8,200	1,000	1,000	≤0,9	182x182	-	219x317x94	•	•
BCE8200-1x	8,200	1,000	1,000	≤0,9	182x182	-	219x317x94	-	•

\* upper edge of the weighing pan to the lower edge of the upper draft shield panel  
x = term for country-specific models

### Learn more with Northern Balance

As UKAS accredited weighing specialists, Northern Balance has been supplying, servicing and calibrating the world's most trusted brands for nearly 50 years. Our customers rely on us for our wealth of product knowledge, quality service and first-class support. Trust us to find an Entris II® solution that meets your weighing needs.

[www.northernbalance.co.uk/entris2](http://www.northernbalance.co.uk/entris2)



Tel: 0344 477 1966  
Email: [hello@northernbalance.co.uk](mailto:hello@northernbalance.co.uk)  
Web: [www.northernbalance.co.uk](http://www.northernbalance.co.uk)